

# Crystal Clear **Maxi Sound** Exclusive **SCR Technology** High Gain **Compact Antenna**

Uniden's 2.4GHz SCR range of phones use a shorter wavelength to deliver clear sound and all the essentials, making them ideal for two-storey houses and single level apartments.


## **XSA 1255**

- Integrated Digital Answering Machine
- Advanced Alpha Display Caller ID
- Crystal Clear Maxi Sound
- Ideal for Two-Storey Houses and Single Level Apartments
- One Touch Rocket Dial




2.4GHz SCR TECHNOLOGY

### Advanced Alpha Display Caller ID\*



- Caller ID\* Capable (Type 1 and Type 2)
- POP ID\* - Caller Name Identification
- 30 Caller ID\* Memories
- Alpha Memory Dialling

### Crystal Clear Maxi Sound



- Extra Loud Handset Volume Control

### Integrated Digital Answering Machine



- With Remote Access

### One Touch Rocket Dial



- Dial your most frequently called VIP number with just one key press



### XS 1215 + 1

- Includes Additional Handset and Charge Cradle
- Advanced Alpha Display Caller ID
- Crystal Clear Maxi Sound
- Ideal for Two-Storey Houses and Single Level Apartments
- One Touch Rocket Dial



### XS 1215

- Advanced Alpha Display Caller ID
- Crystal Clear Maxi Sound
- Ideal for Two-Storey Houses and Single Level Apartments
- One Touch Rocket Dial
- POP ID – Caller Name Identification



### XS 1210

- Crystal Clear Maxi Sound
- Ideal for Two-Storey Houses and Single Level Apartments
- One Touch Rocket Dial
- 14 Days Standby Time
- 10 Speed Dial Locations
- Choice of Black or White





## 2.4GHz SCR Technology

Shorter wavelength improves signal reflection and increases Sound Clarity and Range. Suitable for two-storey houses and single level apartments.

## Notes

---

---

---

---

---

---

---

---



## F.A.Q's

---

**1. Q: What is the major benefit of the SCR Technology series?**

A: These phones are very simple to use and have all the essentials.

---

**2. Q: What is Maxi-Sound?**

A: The Uniden phones use this feature to provide extra loud handset volume control.

---

**3. Q: When would I use Rocket Dial?**

A: This VIP number calling feature is ideal for storing a medical number, or a parent or police number etc.

---

**4. Q: Why does the SS E15 phone use SCR Technology?**

A: The SCR technology is the best suited to the circuitry used in hearing aids so that the user does not experience interference.

---

**5. Q: Does the SS E15 have a telecoil?**

A: Yes, because it has been specially designed for the hard of hearing.



2.4GHz SCR Technology

# Specifications



KEY RANGE FEATURES	XSA 1255**	XS 1215**	XS 1210
2.4GHz SCR Technology	•	•	•
POP ID* - Caller Name Identification	•	•	
Alpha Memory Dialling	•	•	
30 Caller ID* Memories	•	•	
Integrated Digital Answering Machine	•		
Crystal Clear Maxi Sound	•	•	•
Visual Message Waiting & New Call Indicator*		•	
Ideal for 2 Storey Houses & Single Level Apartments	•	•	•
Advanced Alpha Display Caller ID*	•	•	
One Touch Rocket Dial	•	•	•
3 Line Backlit LCD Dot Matrix Display	•	•	
Talk Time	7 Hours	7 Hours	7 Hours
Standby Time	14 Days	14 Days	14 Days
Outgoing Message Time	30 sec		
Incoming Memo/Record Time	4 min(per msg)		
Total Incoming Memo/Record Time	12 min		
Battery	BT-905	BT-905	BT-905
Hearing Aid Compatible	•	•	•
Headset Compatible: HS-910AU	•	•	
Belt Clip	•	•	•
Wall/Desk Mountable	•	•	

\* Caller ID, POP ID and Visual Message Waiting Features only work if you subscribe to the service provided by your telephone company. There is usually a fee for this service. Caller ID Type 2 service has limited availability in New Zealand. Please check with your telephone company.

\*\*Also available in specially packaged models with one or more additional handsets.

Specifications subject to change without notice.